



AQ1280

The AQ1280 appliance uses patented AirQ technology to diffuse Premium Scenting fragrance and odour treatment products into the air.

This appliance is designed for professional use, in direct diffusion or through an HVAC system.

- Diffuse directly or via HVAC system.
- 50 intensity levels and timing options give you control.
- Perfectly scents spaces up to 4,250m²
- AirQ™ droplets are 50 times smaller than a traditional aerosol.



Technical Specifications

- Type:** - Single use nebulizer head
Cartridge: - 2,500 ml recyclable

Power Specifications

- Input:** - 100 – 240 VAC, 0.6 A, 50/60 Hz
Protection: - Switched-mode power supply
Internal: - 3V backup battery
Output: - 15V DCat 1.2A

Performance & Settings

- Coverage:** - Up to 150,000 ft³ (4,250 m³)
Programmes: - Up to 21 start/stop times and intensities
- 24/7 mode
Settings: - 50 intensity levels
Off-cycle: - 2 minutes, or 7 minutes
Enclosure: - Grey fiberglass with swinging door,
NEMA 4 rated
Safety Approval: - UL, CE, & FCC Part 15, ROHS and IFRA
compliant
Environment: - 0° to 40° C, <85% Humidity

Dimensions & Installation

- Size:** - 15½" x 13½" x 6¾" (39.4cm x 34cm x
17.2cm)
Weight: - 13.7 lbs. (6.2kg) with full 2500ml
cartridge
Mounting: - Wall mount, with and without fan
- Tabletop/floor mount, with feet

We are leading the world in developing fine fragrances for the air - this is a very specialist skill that demands empathy, creativity and passion.

Our unique fragrance formulations exceed the most advanced regulations in fragrance safety.

They are distributed via our own advanced, patented diffusion technology and serviced at a consistently high quality level by our in-house experts.